



Customers and Staff benefit from clear communication.
Hearing aid wearers benefit from the use of a portable Infrared loop system.

Being hard of hearing can make people feel isolated. Wearing a hearing aid can help but it amplifies all sounds to the same level. In busy or noisy situations this is more of a hindrance than a help with frequent misunderstandings and frustration. In larger areas such as meeting rooms, cinemas, churches etc it can become difficult to distinguish between what

needs to be heard and what is background noise. The **Infrinity portable infrared system** makes life easier for the hard of hearing. With inputs from dedicated sound sources, be it microphone or line in; hearing aid wearers hear what they need to hear without distracting background noise. The two channel transmitter can also be used to run

audio descriptive commentary or simultaneous translation via the headphone receivers. With the neck loop receiver the hearing aid wearer gets clear sound from source straight to the hearing aid.

With the Infrared loop system ensure hearing aid wearers hear what they need to hear.



Actual colour may vary from reproduced colour

Features:

- Built into case for easy transport
- Easily set up, no cable to run around room
- Line and microphone inputs
- Simultaneous translation or audio description from single transmitter
- Cover large or small areas without fear of overspill
- Multiple systems can be used in the same building without interference
- Reduces distracting background noise

Customers:

- Odeon
- House of Fraser
- Councils
- Theaters
- Schools
- Hospitals
- Many more

Product information:

- | | |
|-------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Type: | Dual channel Infrared loop system |
| Coverage: | Up to 350m2, multiple transmitters can be used to extend the area covered |
| Size transmitter: | 250mmx180mmx75mm |
| Power: | 28VDC |
| Frequency: | 2.3MHz and 2.8MHz simultaneously |
| Inputs: | Left and right line, left and right sync, left and right microphone |
| Outputs: | Left and right sync |
| Accessories: | Infrared induction loop Transmitter, two channel
Infrared headphone receiver, two channel 2.3 and 2.8MHz switchable
Infrared body pack and neck loop receiver, two channel 2.3 and 2.8MHz switchable |
| Warranty: | 12 months. Extended warranty available |